## TABER<sup>®</sup> Linear Abraser Set-Up Options



The following chart is provided to assist in establishing a specific test load<sup>1</sup>. To calculate the total load, sum the combined weights of the system:

TOTAL LOAD = Spline Shaft + Weight Support (optional) + Auxiliary Weight Disc(s) (optional) + Attachment

Spline Shaft			Wear & Abrasion			Scratch / Mar		
	-			Attachments			Attachments	
130855	Spline Kit, steel 10mm diam. x 300mm	180g	130852	Wearaser Collet Kit, stainless steel	98g	133566	90° Multi-Mar Scratch, w/ loop stylus	100g
132190	Spline Kit, aluminum 10mm diam. x 300mm	85g	131852	Wearaser Collet Kit, aluminum	28g	133136	45° Multi-Mar Scratch, w/ loop stylus	95g
132280	Spline Kit, aluminum 10mm diam. x 150mm	41g	131852-1	Wearaser Collet Kit, <i>plastic</i>	16g	135025	Needle Stylus (for MultiMar Scratch)	
	Weight Support		131862	Wearaser Collet Kit, <i>jumbo</i>	43g	133139	Hoffman Stylus (for MultiMar Scratch)	
133554	Weight Support, for <i>steel</i> <i>spline shaft</i> 350g base load	72g	130572	Universal Attachment, stainless steel 25.4mm dia.	98g	133178	Copper Coin (for MultiMar Scratch)	
133556	Weight Support, for <i>alumi-</i> num shaft 350g base load	167g	135430	Universal Attachment, aluminum 50.8mm dia.	98g	135447-1	Stainless Steel Coin (for MultiMar Scratch)	
Auxiliary Weight Discs			132735	Precision Knuckle Attachment	135g	133553	Conical Scratch Tip, 0.10mm Diameter	9g
132716	Auxiliary Weight Disc, 10g	10g	130570	Crockmeter Kit 16mm dia.	166g	133555	Conical Scratch Tip, 0.25mm Diameter	9g
132717	Auxiliary Weight Disc, 20g	20g	134571	Crock Block Kit w/holder 19mm x 25.4mm	166g	135167	Conical Scratch Tip, 0.30mm Diameter	10g
131548	Auxiliary Weight Disc, 50g	50g	132700	Square Crock Finger, requires Crockmeter Kit	28g	133557	Conical Scratch Tip, 0.40mm Diameter	10g
131611	Auxiliary Weight Disc, 75g	75g	134550	Rectangular Crock Block, 40mm x 85mm	170g	133559	Conical Scratch Tip, 0.50mm Diameter	10g
131612	Auxiliary Weight Disc, 100g	100g	134298	Special Crock Attachment, stainless steel; R10mm	125g	135166	Conical Scratch Tip, 0.60mm Diameter	10g
135174	Auxiliary Weight Disc, 110g	110g	135681	Rubbing Adapter C, requires Crockmeter Kit	172g	135243	Conical Scratch Tip, 0.75mm Diameter	10g
131373	Auxiliary Weight Disc, 150g	150g	134656	10mm Padded Square Finger Attachment	27g	134622	Conical Scratch Tip, 1.0mm Diameter	10g
130285	Auxiliary Weight Disc, 250g	250g	134658	20mm Padded Square Finger Attachment	39g	135193	Hemisphere Scratch Tip, 1.0 mm dia steel w/HRC60-66	9.5g
134218-1	Auxiliary Weight, 1000g	1000g	134985	Steel Wool Holder Kit	22.5g	132347	Hemisphere Scratch Tip, 1.0 mm dia tungsten carbide	9.5g
134218-2	Auxiliary Weight, 2000g	2000g	133432	ScotchBrite <sup>™</sup> Abrasive Pad Kit	58g	135627	Hemisphere Mar Tip, 3.0 mm dia tungsten carbide	10.5g
132740	Precision Weight Kit, (mounts to spline shaft)	Min. 7g	133450	Brass Brush Holder Attachment Kit	79g	132348	Hemisphere Mar Tip, 7.0 mm dia tungsten carbide	11.5g
132710	Precision Weight Post, (mounts to weight holder)	Min. 35g	133423	Test Wedge Kit, includes SiC 320 sandpaper	180g	130575	Scratch Kit, Stainless Steel w/ Conical Diamond Tool	98g
	Accessories		134380	Wire Scrape Attachment, 1mm diam. wire	81g	131604	Scratch Kit, Aluminum w/ Conical Diamond Tool	33g
131877	Multi-Head Attachment, with aluminum spline shaft		134495	Wire Scrape Attachment, 0.635mm diam. wire	81g	132892 132910	Diamond Tool Holder, w/ 90° Conical Diamond Tool	9g
131877-1	Multi-Head Attachment, with steel spline shaft		133060 134887	Wire/Cable Scrape Abrasion Kit	63g	134981	Diamond Tool Holder, w/ 60° Conical Diamond Tool	9g
			133370 134583	Flexible Material Abrasion Kit	17g	133475	Scraper, 5mm	37g
		d				133476	Scraper, 10mm	46g
						131716	Coin Holder Kit, 45; 60; or 75 degree	40g
							Doncil Hardnord Scratch Kit	T

## NOTES:

a) The standard load is 350g (includes mass of spline shaft; weight support; and steel wearaser collet kit).

b) If no accessory weight discs are required, it is possible to reduce the load by removing the weight support.

c) The maximum number of 250g weight discs that should be applied to the weight support is:

133554 – 5 discs 133556 – 7 discs

d) Recommended *Maximum* loads:

Spline Kit, steel (130855):	2400 grams
Spline Kit, aluminum (132190):	2100 grams
Spline Kit, aluminum (132280):	2100 grams

e) T-Slot Universal Table (133336) or Universal Specimen Table (131734) are strongly recommended.

<sup>1</sup> Mass of attachments are for information purposes only, and do not include tolerances



Pencil Hardness Scratch Kit

includes weight of pencil

34g

133453